


# U3VQPQXTR

## Base Product



Ultra Low Loss (ULL) OM5 MPO8 (Non-Pinned) to MPO8 (Pinned), Fiber Trunk Cable Assembly, 16-Fiber, LZSH B2ca

## Product Classification

Regional Availability	Europe
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	Propel   SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

## General Specifications

Connector A, quantity	2
Color, boot A	Gray
Color, connector A	Lime green
Connector B, quantity	2
Color, boot B	Gray
Color, connector B	Lime green
Construction Type	Stranded
Furcation Color	Lime green
Interface, Connector A	MPO-08/UPC Female
Interface, Connector B	MPO-08/UPC Male
Jacket Color	Lime green
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	8
Total Fibers, quantity	16


## Dimensions

Breakout Length	22 in
Cable Assembly Length Range (m)	3 – 305

# U3VQPQXTR

Cable Assembly Length Range (ft)10 – 999

## Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum11.24 lb @ 0 ° | 4.40 lb @ 90 °

## Optical Specifications

Fiber ModeMultimode  
Fiber TypeOM5, LazrSPEED®

## Environmental Specifications

Operating Temperature-10 °C to +60 °C (+14 °F to +140 °F)  
EN50575 CPR Cable EuroClass Fire PerformanceB2ca  
Environmental SpaceIndoor | Low Smoke Zero Halogen (LSZH)

## Regulatory Compliance/Certifications

AgencyANATEL  
ClassificationCompliant  
ISO 9001:2015Designed, manufactured and/or distributed under this quality management system



## Included Products

# U3VQPQXTR

---

760253107 N-016-MP-5G-F08LM/20T/B2	–	Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 16 fiber with 8 fiber 2.0mm subunits, Gel-free, Multimode OM5, Meters jacket marking, Lime green jacket color, B2ca flame rating
860659020	–	MPO-08, ULTRA LOW LOSS, MALE, OM5, LIME-GREEN, 2mm
860659026	–	MPO-08, ULTRA LOW LOSS, FEMALE, OM5, LIME-GREEN, 2mm