
## UGXQZQZTM

#### **Base Product**



Ultra Low Loss (ULL) OM4 MPO8 APC (Pinned) to MPO8 APC (Pinned), Fiber Trunk Cable Assembly, 144-Fiber, Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

#### General Specifications

Connector A, quantity 18

Color, boot A Gray

Color, connector A Green

Connector B, quantity 18

Color, boot B Gray

Color, connector B Green

Construction Type Stranded

Furcation Color Aqua

Interface, Connector A MPO-08/APC Male

Interface, Connector B MPO-08/APC Male

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 144

Dimensions




# UGXQZQZTM

Cable Assembly Length Range (ft)

Breakout Length 22 in

Cable Assembly Length Range (m) 3 - 305

#### Ordering Tree



10 - 999

#### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

Optical Specifications

Fiber Mode Multimode

**Fiber Type** OM4, LazrSPEED®

## **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



# UGXQZQZTM



### Included Products

760248186 P-144-MP-5K-F08AQ/20T

860662230

- Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 144 fiber multi-unit with 8 fiber subunits,
   Multimode OM4, Gel-free, Feet jacket marking, Yellow jacket color
- MPO8,ULL,Multimode,MALE,APC,GREEN,2 mm

