

CB-12-50



Cable Banding, Bulk, 1/2 in x 50 ft Reel (uses CB-LH-25 Locking Heads - not incl)

Product Classification

Product Type	Banding
Product Brand	PIM-Guard®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Adapter Type	Adapter
Color	Black
Mounting	Round member

Dimensions

Width	12.7 mm 0.5 in
Length	15.24 m 50 ft
Material Thickness	1.524 mm 0.06 in

Material Specifications

Material Type	Heat-stabilized weather resistant acetal
----------------------	--

Mechanical Specifications

Tensile Force	1,112.055 N 250 lbf
----------------------	-----------------------

Environmental Specifications

Installation temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Operating Temperature	-65 °C to +90 °C (-85 °F to +194 °F)

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

CB-12-50

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

CSA

Compliant

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

