

NOVUX™ Hardened Mulfi-fiber Terminal, 6 HMFOC ports, 2 fibers per port, Flat toneable loose tube cable, 1000 ft/304 m, with universal mounting bracket

- NOVUX™ Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ HMT terminals are well suited for fiber-rich applications and available with 12 or 24 Fibers; no internal splitter option
- Available with flat dielectric up to 24 fiber or flat toneable/locatable up to 12 fiber. Terminals can
  be used as a distribution point within a network or as a final multifiber drop terminal where more
  than a single fiber is required to service an SFU or cellular tower
- NOVUX™ smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

#### **Product Classification**

Regional Availability

Asia | EMEA | Latin America | North America

Product Type Access terminal, without splitter/tap

 Product Brand
 NOVUX™

 Product Series
 HMT

Minimum Order Quantity 1

#### General Specifications

Cable Type Toneable - Flat - Loose Tube

Cable, quantity 1

**Distribution Type** 6 ports, 2 fibers per port

**Drop Port Type**Hardened multi-fiber (HMFOC) jack, male/pinned

Enclosure Color Black (RAL 9005)

Multi-fiber Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Multi-fiber Port, quantity 6

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened multi-fiber (HMFOC) jack, male/pinned



Port, quantity 6

Stub Type Stub tail

**Dimensions** 


 Height
 80 mm | 3.15 in


 Width
 79 mm | 3.11 in

 Length
 255 mm | 10.039 in

 Cable Length, stub
 1000 ft (304 m)

### Dimension Drawing






Port Configuration

COMMSC PE°

| NOVUX HT   | TECHNOLOGIES AVAILABLE | SMALL                           | MEDIUM                   | LARGE             |
|------------|------------------------|---------------------------------|--------------------------|-------------------|
| HMT Series | Multi-fiber            | Up to 24f                       | Up to 24f                | Up to 24f         |
|            |                        | 2 ports, each 2, 4, 6, 8 or 12f | 6 ports, each 2, 3 or 4f | 12 ports, each 2f |
|            |                        | 3 ports, each 2, 4, 6, or 8f    | 8 ports 2 or 3f          |                   |
|            |                        | 4 ports, each 2, 4, or 6f       |                          |                   |

#### Ordering Tree



#### Material Specifications

Enclosure Material Type Hardened plastic

**Optical Specifications** 

**Fiber Type** G.657.A1/A2

**Operating Wavelength Range** 1260 – 1635 nm

**Attenuation Single Ports, maximum** 0.65 dB

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

**Return Loss, Connector, typical** 65 dB

#### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$ 

**Relative Humidity** 5%–100%, condensing

Environmental Space Above ground | Below ground

Qualification Standards IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

**COMMSCOPE®** 

**UV Resistance** UV stabilized

Packaging and Weights

**Included** Universal mounting bracket

Packaging quantity 1

Packaging Type

Box | Universal spool, wood: terminal is on the top of the spool, stub deploys first

#### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

