

RT-SF12-3-96



High Capacity Penetrating Roof Frame, 12 ft face, three 2-7/8 in OD x 96 in pipes

Product Classification

Product Type Rooftop sector frame

General Specifications

Mounting Penetrating

Pipe, quantity 3

Dimensions

Height 2,438.4 mm | 96 in

Face Width 3.81 m | 12.5 ft

Width 3,810 mm | 150 in

Length 1.311 m | 4.3 ft

Pipe Length 2,438.4 mm | 96 in

Face Support Pipe Diameter 73.152 mm | 2.88 in

Pipe Outer Diameter 73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Frame | Plain end pipes

Regulatory Compliance/Certifications

RT-SF12-3-96

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

