## F028BBS3



FlexTwist® Flexible Twist for WR28, 26.5–40.1 GHz, with interface types UG-599/U and UG-599/U, 900 mm

### **Product Classification**

Product Type Rectangular waveguide, flexible twist

Product Brand FlexTwist®

General Specifications

ComponentFlexible TwistInterfaceUG-599/UInterface 2UG-599/U

**Dimensions** 

 Length
 900 mm | 35.433 in

 Waveguide Size
 WR28 | WG22 | R320

**Electrical Specifications** 

**Attenuation** 3.28 dB/m | 1 dB/ft

Average Power 75 W

**Operating Frequency Band** 26.5 – 40.1 GHz

 Peak Power
 20 kW

 VSWR
 1.3

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)38 mm | 1.496 inMinimum Bend Radius, Multiple Bends (H Plane)76 mm | 2.992 in

 Maximum Twist
 510 °/m | 155.448 °/ft

 Pressurization, maximum
 0.31 N/mm² | 45 psi



# F028BBS3

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

