TW-N10-5NM



Torque Wrench for coupling torque of Nex10 connectors, 11 mm opening

Product Classification

Product Type Wrench

Ordering Note CommScope® non-standard product

General Specifications

Application Accepts 1 x Ø15 mm fiber-cable or 1x Ø 6/10 mm flex-tube | Torques Nex10 connectors

Calibration 6 mo

Tool Type Torque wrench

Dimensions

Wrench Opening 10.922 mm | 0.43 in

Material Specifications

Material Type Steel

Mechanical Specifications

Torque Tolerance +0/-1 N-m (+0/-8.85 in-lb)

Torque Value 44.25 in lb | 5 N-m

Packaging and Weights

Height, packed 284.48 mm | 11.2 in

Length, packed 279.4 mm | 11 in

Packaging quantity 1

Weight, gross 0.89 kg | 1.962 lb

