



M4800 DDM for G2-modules, Black (5 ea/pkg)

Product Classification

Regional Availability	Asia Europe Latin America
Portfolio	CommScope®
Product Type	Bezel

General Specifications

Color	Black
--------------	-------

Dimensions

Height	43.688 mm 1.72 in
Width	229.108 mm 9.02 in
Depth	17.018 mm 0.67 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0

Packaging and Weights

Packaging quantity	5
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

760253194 | M4800-G2-DDM-5

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

