

760254042 | EPX-1U-CHD-ENC-FX



EPX 1U fixed panel, accepts (8) CHD style modules, adapter packs, or splice cassettes, providing up to 48 duplex LC ports

Product Classification

Regional Availability	Asia Australia/New Zealand China
Portfolio	CommScope®
Product Type	Fiber patch panel Fiber patch/splice panel
Product Series	EPX

General Specifications

Application	Accepts eight CHD modular cassettes
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	4
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Fixed
Total Fibers, quantity	96
Total Ports, quantity	0

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	412.75 mm 16.25 in

Environmental Specifications

Safety Standard	CSA 22.2 UL 1863
------------------------	--------------------

Packaging and Weights

760254042 | EPX-1U-CHD-ENC-FX

Packaging quantity 1
Weight, net 2.994 kg | 6.6 lb