


# MC-CP12S-B



3-Sector Monopole Co-location Platform Base Kit, 10 in to 30 in OD, 12 ft 6 in face, pipe ordered separately

## OBSOLETE

This product was discontinued on: March 9, 2022

### Replaced By:

MC-CP12M-B

3-Sector Monopole Co-location Platform Base Kit, 12 in to 50 in OD, 12 ft 6 in face, pipe ordered separately

## Product Classification

**Product Type** Monopole platform kit

## General Specifications

**Mounting** Monopole, 254–762 mm (10–30 in) OD

**Pipe, quantity** 0

**Sectors, quantity** 3

## Dimensions

**Face Width** 3.81 m | 12.5 ft

**Width** 3810 mm | 150 in

**Mounting Diameter, maximum** 762 mm | 30 in

**Mounting Diameter, minimum** 254 mm | 10 in

**Pipe Outer Diameter** 60.96 mm | 2.4 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 100 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

**Wind Rating Test Method** TIA/EIA-222

# MC-CP12S-B

---

## Packaging and Weights

<b>Included</b>	Platform   Rail   Ring mount
<b>Packaging quantity</b>	1
<b>Weight, net</b>	643.194 kg   1418 lb

## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--