


# MCG23HDX-14M-9-126



G23HDX High Capacity 3-Sector Monopole Frame, 14.5 ft 2.88 in OD face pipes, includes nine 2.88 OD 126 in pipes; For patents, see [www.cs-pat.com](http://www.cs-pat.com).

## OBSOLETE

This product was discontinued on: July 29, 2022

### Replaced By:

MCG23HDX-14M12120 G23HDX High Capacity 3-Sector Monopole Sector Frame, 14.5 ft x 2.88 in OD face pipes, includes twelve 2.88 OD x 120 in pipes

## Product Classification

**Product Type** High capacity monopole sector frame

## General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

**Pipe, quantity** 9

**Sectors, quantity** 3

## Dimensions

**Height** 3,200.4 mm | 126 in

**Face Width** 4.42 m | 14.5 ft

**Width** 4,419.6 mm | 174 in

**Pipe Length** 3,200.4 mm | 126 in

**Face Support Pipe Diameter** 73.025 mm | 2.875 in

**Mounting Diameter, maximum** 1270 mm | 50 in

**Mounting Diameter, minimum** 381 mm | 15 in

**Pipe Outer Diameter** 73.025 mm | 2.875 in

**Stand-off Distance** 1,165.86 mm | 45.9 in

## Material Specifications

**Material Type** Hot dip galvanized steel

# MCG23HDX-14M-9-126

---

## Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact <a href="mailto:steelproducts@commscope.com">steelproducts@commscope.com</a> or call 800-255-1479
<b>Wind Rating Test Method</b>	TIA/EIA-222

## Packaging and Weights

<b>Included</b>	Pipe mounts   Plain end pipes (9)   Ring mounts (2)   Sector frames (3)   Stiff arm
<b>Packaging quantity</b>	1
<b>Weight, net</b>	1,262.348 kg   2783 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--