


# PGP-CS10

---



Polymer PIM-Guard Antenna and RRU Cable Support Bracket with 10 positions / 20 cables for stackable hangers (up to 2 per position)

Compatible with first and second generation Polymer PIM-Guard products

-SSH-1416

-SSH-411

-SSH-1117

## Product Classification

**Product Type** Support bracket

**Product Brand** PIM-Guard

## General Specifications

**Cable Runs, quantity** 10

**Hole, quantity** 10

**Mounting** Round member

## Dimensions

**Height** 50.8 mm | 2 in

**Width** 304.8 mm | 12 in

**Length** 304.8 mm | 12 in

**Mounting Diameter, maximum** 60.96 mm | 2.4 in


**Mounting Diameter, minimum** 60.96 mm | 2.4 in

**Hole Size** 3/4 in

## Ordering Tree

# PGP-CS10

---



## Material Specifications

**Material Type** Polymer

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 0.82 kg | 1.808 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

