UJXMXMXCP

Base Product



Ultra Low Loss ULL LazrSPEED® 550 MPO(Pinned) to MPO(Pinned) Pre-terminated Trunk Cable, MPO12, 288-Fiber, LSZH, 12 fiber PmP 2.0 mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Product Brand Propel

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

 Color, boot A
 Black

 Color, connector A
 Black

 Color, boot B
 Black

 Color, connector B
 Black

 Construction Type
 Stranded

 Furcation Color
 Aqua

 Interface, Connector A
 MPO-12/UPC Male

 Interface, Connector B
 MPO-12/UPC Male

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 288


Dimensions

Breakout Length22 inCable Assembly Length Range (m)3 - 999Cable Assembly Length Range (ft)10 - 999

COMMSCOPE®

UJXMXMXCP

Ordering Tree



Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

EN50575 CPR Cable EuroClass Fire Performance Doa

Environmental Space Dual Rated LSZH/Riser | Indoor

Included Products

COMMSCOPE®

UJXMXMXCP

760249632

N-288-MP-5K-F12AQ/20T/B2

Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 288 fiber with 2.0 mm Subunits, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color, B2ca flame rating

860659006

MPO12, ULL, MALE, OM3/4, AQUA, 2MM

