

MUK-MSK5 | LARGE CROSSOVER PLATE



Large Crossover Plate, connects 2-3/8" - 2-7/8" pipes to 4" - 4-1/2" pipes

Product Classification

Product Type Clamp plate

General Specifications

Mounting Crossover plate

Dimensions

Mounting Diameter 2, maximum 114.3 mm | 4.5 in

Mounting Diameter 2, minimum 101.6 mm | 4 in

Mounting Diameter, maximum 73.025 mm | 2.875 in

Mounting Diameter, minimum 60.325 mm | 2.375 in

Material Specifications

Material Type Hot dip galvanized steel

Environmental Specifications

EPA with 1/2 in (12 mm) radial ice ft²

Packaging and Weights

Included Plates | U-bolts

Packaging quantity 1

* Footnotes

EPA with 1/2 in (12 mm) radial ice EPA—Effective Projected Area