

760256133 | PPL-DM-12AP-12LC-SM-AF



Propel ULL Singlemode MPO-12 Distribution Module, 6 duplex LC to 1X12f MPO/APC pinned, Method A Pairs Flipped

- Ultra-low loss (ULL) with Method A polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 3 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	Propel
Product Series	PPL

General Specifications

Functionality	Breakout
Color, front	Blue
Color, rear	Black
Interface, front	LC/UPC
Interface Feature, front	Internal shutters
Interface, rear	MPO
Interface Feature, rear	Internal shutters Key up/down MPO Pinned Standard
Polarity	Method A Pairs, flipped
Total Fibers, quantity	12
Total Ports, quantity, front	6
Total Ports, quantity, rear	1

Dimensions

Height	11 mm 0.433 in
Width	98 mm 3.858 in
Depth	170 mm 6.693 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.6 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	CE CSA UL UL 62368

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

