



Wall-mountable Optic fiber outlet with 2 LC/APC shuttered Duplex adapters and no pigtails, for ANT splice protection

- Laser safe with in-built individual shutters
- Can be used for entering with a blown fiber tube and storing the Gasblock
- Satellite wall outlet possibility for a second living unit
- Safety cap on drop ports against easy removal

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Outlet
<b>Minimum Order Quantity</b>	10

## General Specifications

<b>Color</b>	White
<b>Distribution Type</b>	6 ports
<b>Mounting</b>	Wall mount
<b>Patch Cord Routing</b>	Downward
<b>Patching Capacity, maximum</b>	6
<b>Pigtails Included, quantity</b>	1

## Dimensions

<b>Height</b>	120 mm   4.724 in
<b>Width</b>	105 mm   4.134 in
<b>Depth</b>	34 mm   1.339 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2
<b>Performance Grade</b>	Standard C grade

## Environmental Specifications

<b>Storage Temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Environmental Space</b>	Indoor
<b>Flammability Rating</b>	UL 94 V-0

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

<b>Performance Grade</b>	Guarantee to meet IEC 61755-1 Random Mating requirement
--------------------------	---