


SFG22HD-10-B



G22HD High Capacity Sector Frame with 2 7/8in OD x 10.5ft face. Base Kit Only. No antenna pipes.

Product Classification

Regional Availability	North America
Product Type	High capacity Tower sector frame
Product Series	G2
Ordering Note	ANDREW® standard product in the United States and Canada
Warranty	One year

General Specifications

Application	4G LTE antenna/radio mount
Mounting	Angle 60°, 203.2 mm (8 in) Straight or tapered legs up to 203.2 mm (8 in) OD
Patent Number	Patent pending
Pipe, quantity	0
Sectors, quantity	1
Tower Taper	Non-tapered Tapered

Dimensions

Face Width	3.2 m 10.5 ft
Width	3,200.4 mm 126 in
Face Support Pipe Diameter	73.025 mm 2.875 in
Mounting Diameter, maximum	218.44 mm 8.6 in
Mounting Diameter, minimum	38.1 mm 1.5 in
Stand-off Distance	1,041.4 mm 41 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
--------------------	---

SFG22HD-10-B

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Frame | Stiff arms (2) | Tower attachment

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code