760255254 | HCA-ACC-FEMALE-FULLSIZE-CVTR



Prodigy Full Size Female Converter

• Prodigy converters simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

Product Type Fiber converter

Product Brand PRODIGY™

Product Series HCA

General Specifications

 Color, boot A
 Black

 Color, connector A
 Black

 Interface, Connector A
 Prodigy

Interface, Connector B Hardened full-size SC/APC

Mechanical Specifications

Dust Cap Pulling Force, minimum 445 N | 100.04 lbf

Optical Specifications

Insertion Loss, maximum0.3 dBInsertion Loss, typical0.15 dBReturn Loss, minimum65 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to +75 $^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +167 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to +70 $^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Environmental Space Outdoor

Qualification Standards IEC 60793 | IEC 60794



760255254 | HCA-ACC-FEMALE-FULLSIZE-CVTR

Packaging and Weights

Packaging quantity

25

