




NOTES:

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ECR 8000023009: RELEASE TO PRODUCTION PER EAO 604203.	05SEP17 JOY	CC/W.XT
B	ECR 8000034693: CAUTION LABELS ADDED.	28MAR19 KC	KJ / SRT
C	ECR 8000036581: UPDATE DRAWING WITH LATEST MODEL.	31JUL19 QF	ZHWJ/REX
D	ECR 40153087CMO: UPDATE DRAWING WITH LATEST MODEL.	26AUG22 FFJ	PL.TANG/HANSEN.W



JAH4-65B-R4

COMMSCOPE, INC. OF NORTH CAROLINA											
TOLERANCES						SAP MATERIAL MASTER					
0 PLACE X ±			2 PLACE .XX ±			1 PLACE .X ±			ANGLES ±		
FINISH						MATERIAL					
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ISO STANDARDS HANDBOOK TECHNICAL DRAWINGS VOLUMES 1 & 2, THIRD EDITION (2002)</small>	NAME	DATE	TITLE								
	CE JOY	09/05/17	PRODUCT DRAWING								
	RW FFAN2	09/06/2022									
	RV										
	AD PLTANG	09/08/2022	SCALE		DOCUMENT NO.						
RE NC1020	09/09/2022	1:5		JAH4-65B-R4-L							
ECN 40153087CMO											
DENSITY	g/mm ³										
MASS	grams										
VOLUME	mm ³										
SURFACE AREA	mm ²										
HEIGHT		SIZE	WORK AREA	BSA	MODEL			DRAWING			SHEET
LENGTH		A2			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	1 OF 1
WIDTH					07	RE	H	03	RE	D	