# PM-412-48



### Adjustable Pipe Mount, 4-1/2 in OD x 48 in

#### **Product Classification**

Product Type Pipe mount

### General Specifications

**Mounting** Saddle mounts

**Note** One 96 in x 8 in panel antenna per pipe mount

Pipe, quantity 1

**Tower Taper** Non-tapered

#### Dimensions

 Height
 1,219.2 mm | 48 in

 Width
 152.4 mm | 6 in

 Length
 152.4 mm | 6 in


 Pipe Length
 1,219.2 mm | 48 in

Pipe Outer Diameter 114.3 mm | 4.5 in



# PM-412-48

# Outline Drawing



## Material Specifications

Material Type Hot dip galvanized steel

# Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL

Wind Rating Test Method TIA/EIA-222

### Packaging and Weights

Included Brackets | Hardware | Pipe

Packaging quantity 1

Page 2 of 3



# PM-412-48

**Weight, net** 20 kg | 44.092 lb

## Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



#### Included Products

MT-653 – Plain End Pipe, 4-1/2 in OD x 48 in x .188" A500C

46Ksi

### \* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

