

# RT-DF14-B

---

High Capacity DUAL Non-Penetrating Roof Frame with 14 ft face - Base Frame only - No Antenna pipes included



## Product Classification

<b>Product Type</b>	Non-penetrating roof frame
<b>Ordering Note</b>	NSTD445 Compliant

## General Specifications

<b>Mounting</b>	Non-penetrating
<b>Pipe, quantity</b>	0

## Dimensions

<b>Face Width</b>	4.42 m   14.5 ft
<b>Width</b>	4,419.6 mm   174 in
<b>Length</b>	2.377 m   7.8 ft
<b>Face Support Pipe Diameter</b>	73.152 mm   2.88 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating Test Method</b>	TIA/EIA-222
--------------------------------	-------------

## Packaging and Weights

<b>Included</b>	Ballast tray   Frame
-----------------	----------------------