

CSC7-D5A1A1BA000



NOVUX™ CSC200 Compact Fiber Closure, splice only, 6 single fiber trays with island, 4 feeder ports, no adapters, no splitters, with mounting bracket, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Single-ended, rectangular fiber closure |
| Product Brand | NOVUX™ |
| Product Series | CSC 200 |

General Specifications

| | |
|---------------------------------------|--|
| Cable Ports Quantity, total | 4 round ports + 12 multi-out ports (24 cables) |
| Cable Sealing Type | Compressed gel |
| Closure Sealing Type | Hinged with latch |
| Closure Style | Single-ended |
| Color | Black |
| Mounting | Pole Wall |
| Port, quantity | 0 |
| Splice Tray Included, quantity | 6 |
| Splice Tray Type Included | 24-way, single fiber slim trays with island |
| Splicing Capacity, maximum | 144 |
| Splitter Type | No splitter |
| Splitter, quantity | 0 |

CSC7-D5A1A1BA000

Dimensions

| | |
|---------------|----------------------|
| Height | 388.2 mm 15.283 in |
| Width | 222 mm 8.74 in |
| Depth | 116 mm 4.567 in |

Environmental Specifications

| | |
|----------------------------|---------------|
| Environmental Space | Outdoor |
| UV Resistance | UV stabilized |

Packaging and Weights

| | |
|---------------------------|-------------------|
| Included | Mounting hardware |
| Packaging quantity | 1 |
| Packaging Type | Box Carton |