

# RR-FM-B

---



Universal Face Mount Base Kit - Brackets Only, pipe ordered separately

## Product Classification

**Product Type** Tower face mount

## General Specifications

**Mounting** Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

**Pipe, quantity** 0

**Tower Taper** Non-tapered | Tapered

## Dimensions

**Height** 1,600.2 mm | 63 in

**Width** 508 mm | 20 in

**Face Support Pipe Diameter** 0 mm | 0 in

**Mounting Diameter, maximum** 203.2 mm | 8 in

**Mounting Diameter, minimum** 0 mm | 0 in

**Pipe Outer Diameter** 0 mm | 0 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamps | Hardware

**Packaging quantity** 1

**Weight, net** 111.992 kg | 246.9 lb

## Regulatory Compliance/Certifications

# RR-FM-B

---

**Agency****Classification**

CHINA-ROHS

Above maximum concentration value

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

