

SA-B10

Stiff Arm / Tieback Bracket, includes 126" pipe



Product Classification

Product Type Stiff arm mount

General Specifications

Mounting Round and angle legs

Pipe, quantity 1

Dimensions

Height 203.2 mm | 8 in

Width 203.2 mm | 8 in

Length 3,200.4 mm | 126 in

Pipe Length 3,200.4 mm | 126 in

Mounting Diameter, maximum 88.9 mm | 3.5 in

Mounting Diameter, minimum 48.26 mm | 1.9 in

Pipe Outer Diameter 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Attachment hardware | Pipe

Packaging quantity 1

Weight, net 22.135 kg | 48.8 lb

Regulatory Compliance/Certifications

SA-B10

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

- SA-B – Stiff Arm /Tieback Brackets for 2-3/8 in OD pipe - Pipe not included