

SA-B12

Stiff Arm / Tieback Bracket, includes 150" pipe



Product Classification

Product Type Stiff arm mount

General Specifications

Mounting Round and angle legs

Pipe, quantity 1

Dimensions

Height 203.2 mm | 8 in

Width 203.2 mm | 8 in

Length 3810 mm | 150 in

Pipe Length 3810 mm | 150 in

Mounting Diameter, maximum 88.9 mm | 3.5 in

Mounting Diameter, minimum 48.26 mm | 1.9 in

Pipe Outer Diameter 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Attachment hardware | Pipe

Packaging quantity 1

Weight, net 24.812 kg | 54.7 lb

Regulatory Compliance/Certifications

SA-B12

Agency

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS



Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted

Included Products

MT-537

- Plain End Pipe, 2-3/8 in OD x 126 in .120" A500C 46Ksi

SA-B

- Stiff Arm /Tieback Brackets for 2-3/8 in OD pipe - Pipe not included