

# PPLUGVDLCUCK



Propel ULL Multimode OM5 Cabled Module, 6x12 duplex LC Propel module on End A to Stub on End B, 72 fiber Plenum Trunk, Method B Enhanced

- This component requires 3 of the 12 lanes on the Propel Panel blade
- Ultra-low loss (ULL) with Method B Enhanced polarity
- End A module can be installed from rear of panel
- Serialized QR code provides easy access to factory optical test results

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	SYSTIMAX®
Product Type	Fiber cabled module
Product Brand	Propel
Product Series	PPL
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters   Maximum length is 400 meters

## General Specifications

Configuration Type	PROPEL Module to Stub
Cable Color	Lime green
Cable Type	Trunk Cable - Plenum
Interface, front	LC/UPC
Interface Feature, front	Duplex   Shuttered
Interface Color, front	Lime green
Interface, rear	Stub
Module Size, end A	12 fiber
Module Quantity, end A	6
Polarity	Method B Enhanced (ULL)
Total Fibers, quantity	72
Total Ports, quantity, front	36

## Dimensions

Height	11 mm   0.433 in
--------	------------------

# PPLUGVDLCUCK

Width	196 mm   7.717 in
Depth	170 mm   6.693 in
Breakout Length, end B	0 in
Cable Assembly Length Range (m)	1 – 400
Cable Assembly Length Range (ft)	2 – 999

## Ordering Tree



## Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM5
Insertion Loss, maximum	0.35 dB

## Environmental Specifications

Qualification Standards	IEC 61753-1   TIA-568.3-D
Safety Standard	c-UL-us

## Packaging and Weights

Packaging quantity	1
--------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

# PPLUGVDLCUCK

---

UK-ROHS

Compliant/Exempted



## Included Products

760242121 P-072-MP-5G-F12LM/20T	–	Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 72 fiber multi-unit with 12 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color
------------------------------------	---	--------------------------------------------------------------------------------------------------------------------------------------------------------------------