

# PPLUGXRLCLCH



Propel ULL Multimode OM4 Cabled Module, 3x16 duplex LC Propel module on End A to 3x16 on End B, 48 fiber Plenum Trunk, Method B Enhanced

- This component requires 4 of the 12 lanes on the Propel Panel blade
- Ultra-low loss (ULL) with Method B Enhanced polarity
- End A module can be installed from rear of panel
- Serialized QR code provides easy access to factory optical test results

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America   |
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Product Type</b>          | Fiber cabled module   |
| <b>Product Brand</b>         | Propel  |
| <b>Product Series</b>        | PPL   |
| <b>Ordering Note</b>         | End B module is the same module as End A   For lengths greater than 999 ft (304 m), orders must be in meters   Maximum length is 400 meters |

## General Specifications

|                                 |                                |
|---------------------------------|--------------------------------|
| <b>Configuration Type</b>       | PROPEL Module to PROPEL Module |
| <b>Cable Color</b>              | Aqua                           |
| <b>Cable Type</b>               | Trunk Cable - Plenum           |
| <b>Interface, front</b>         | LC/UPC                         |
| <b>Interface Feature, front</b> | Duplex   Shuttered             |
| <b>Interface Color, front</b>   | Aqua                           |
| <b>Interface, rear</b>          | LC/UPC                         |
| <b>Interface Feature, rear</b>  | Duplex   Shuttered             |
| <b>Interface Color, rear</b>    | Aqua                           |
| <b>Module Size, end A</b>       | 16 fiber                       |
| <b>Module Size, end B</b>       | 16 fiber                       |
| <b>Module Quantity, end A</b>   | 3                              |
| <b>Module Quantity, end B</b>   | 3                              |
| <b>Polarity</b>                 | Method B Enhanced (ULL)        |

# PPLUGXRLCLCH

|                                     |    |
|-------------------------------------|----|
| <b>Total Fibers, quantity</b>       | 48 |
| <b>Total Ports, quantity, front</b> | 24 |
| <b>Total Ports, quantity, rear</b>  | 24 |

## Dimensions

|   |                   |
|---|-------------------|
| <b>Height</b>                           | 11 mm   0.433 in  |
| <b>Width</b>                            | 131 mm   5.157 in |
| <b>Depth</b>                            | 170 mm   6.693 in |
| <b>Breakout Length, end B</b>           | 23 in             |
| <b>Cable Assembly Length Range (m)</b>  | 1 – 400           |
| <b>Cable Assembly Length Range (ft)</b> | 2 – 999           |

## Ordering Tree



## Optical Specifications

|                                |           |
|--------------------------------|-----------|
| <b>Fiber Mode</b>              | Multimode |
| <b>Fiber Type</b>              | OM4       |
| <b>Insertion Loss, maximum</b> | 0.35 dB   |

## Environmental Specifications

|                                |                           |
|--------------------------------|---------------------------|
| <b>Qualification Standards</b> | IEC 61753-1   TIA-568.3-D |
| <b>Safety Standard</b>         | c-UL-us                   |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

# PPLUGXRLCLCH

---

| Agency     | Classification                    |
|------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS       | Compliant/Exempted                |
| UK-ROHS    | Compliant/Exempted                |



## Included Products

- 760251000 - Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 48 fiber multi-unit with 16 fiber subunits, P-048-MP-5K-F16AQ Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color