



any pigtails and/or adapters are not shown in the image



## HFTP-AM Customer premises fiber wall outlet, four pigtails, two Duplex LC/APC adapter with inner shutters

- Compact fiber wall outlet for use at the final fiber termination point in the customer premises
- Can be wall mounted and mounted on wall boxes with fixation points of 60mm
- Direct termination with field installable connectors
- Laser safe with in-built individual shutters

### Product Classification

<b>Product Type</b>	Fiber wall outlet
<b>Product Series</b>	HFTP
<b>Minimum Order Quantity</b>	75

### General Specifications

<b>Color</b>	White
<b>Cover Type</b>	Screw-on
<b>Interface Type</b>	LC/APC
<b>Mounting</b>	Wall mount
<b>Pigtails Included, quantity</b>	0
<b>Total Ports, quantity</b>	1

### Dimensions

<b>Height</b>	104.902 mm   4.13 in
<b>Width</b>	84.836 mm   3.34 in
<b>Depth</b>	24.892 mm   0.98 in

### Material Specifications

<b>Material Type</b>	LSZH thermoplastic
----------------------	--------------------

### Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

### Environmental Specifications

<b>Storage Temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)
----------------------------	--------------------------------------

# 760256174 | HFTP-AM-L242-E

---

**Relative Humidity** Up to 93%, non-condensing

**Environmental Space** Indoor

## Packaging and Weights

**Packaging quantity** 75