TP-MSC-68



Multi-Sector Cluster Bracket, 6 in –8 in OD



Product Classification

Product Type Tripod mount component

General Specifications

Mounting Round member,152.4–203.2 mm (6–8 in) OD

Dimensions

 Height
 101.6 mm | 4 in

 Width
 330.2 mm | 13 in

 Length
 0.335 m | 1.1 ft

 Pipe Outer Diameter
 60.96 mm | 2.4 in

 Stand-off Distance
 114.3 mm | 4.5 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included Brackets | U-bolts

Packaging quantity 1

Weight, net 21.2 kg | 46.738 lb

Regulatory Compliance/Certifications

Agency Classification

COMMSCOPE®

TP-MSC-68

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

