

# TTS3-56

---



Three-way Stand-off Adapter Kit for 5–6 in round members, includes UAAI insert

## Product Classification

<b>Product Type</b>	Adapter
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Adapter Type</b>	Stand-off adapter
<b>Mounting</b>	3/4 in through hole

## Dimensions

<b>Material Thickness</b>	2.591 mm   0.102 in
---------------------------	---------------------

## Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

## Mechanical Specifications

<b>Maximum Loading</b>	Double stack, 1-5/8 in cable
------------------------	------------------------------

## Packaging and Weights

<b>Height, packed</b>	12 cm   4.724 in
<b>Width, packed</b>	11 cm   4.331 in
<b>Length, packed</b>	1 cm   0.394 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.58 kg   1.279 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

# TTS3-56

---

REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

- |         |   |
|---------|---|
| 31670-5 | - Round Member Adapter for 5-6 in round members |
| SA-38   | - Three-way Snap-in Stand-off Adapter           |
| UAAI    | - Universal Angle Adapter Insert                |

# 31670-5

---



## Round Member Adapter for 5–6 in round members

### Product Classification

<b>Product Type</b>	Adapter
<b>Ordering Note</b>	CommScope® standard product (Global)

### General Specifications

<b>Adapter Type</b>	Round member adapter
---------------------	----------------------

### Dimensions

<b>Compatible Diameter, maximum</b>	152.4 mm   6 in
<b>Compatible Diameter, minimum</b>	127 mm   5 in
<b>Material Thickness</b>	0.711 mm   0.028 in

### Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

### Mechanical Specifications

<b>Maximum Loading</b>	Triple stack, 1-5/8 in cable
------------------------	------------------------------

### Packaging and Weights

<b>Height, packed</b>	36 cm   14.173 in
<b>Width, packed</b>	27 cm   10.63 in
<b>Length, packed</b>	8 cm   3.15 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.51 kg   1.124 lb

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>

# 31670-5

---

ROHS Compliant


UK-ROHS Compliant



# SA-38

---

## Three-way Snap-in Stand-off Adapter



### Product Classification

<b>Product Type</b>	Adapter
<b>Ordering Note</b>	CommScope® standard product (Global)

### General Specifications

<b>Adapter Type</b>	Stand-off adapter
<b>Mounting</b>	3/4 in through hole   3/8 in through hole   Round member

### Dimensions

<b>Height</b>	2.54 mm   0.1 in
<b>Outside Width</b>	41.402 mm   1.63 in
<b>Outside Length</b>	85.852 mm   3.38 in
<b>Material Thickness</b>	2.591 mm   0.102 in

### Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

### Mechanical Specifications

<b>Maximum Loading</b>	Double stack, 1-5/8 in cable
------------------------	------------------------------

### Packaging and Weights

<b>Height, packed</b>	12 cm   4.724 in
<b>Width, packed</b>	11 cm   4.331 in
<b>Length, packed</b>	1 cm   0.394 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.58 kg   1.279 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





## Universal Angle Adapter Insert

### Product Classification

<b>Product Type</b>	Adapter
<b>Ordering Note</b>	CommScope® non-standard product

### General Specifications

<b>Adapter Type</b>	Adapter
<b>Mounting</b>	3/8 in tapped hole

### Dimensions

<b>Outside Width</b>	12.7 mm   0.5 in
<b>Outside Length</b>	25.4 mm   1 in
<b>Material Thickness</b>	12.7 mm   0.5 in

### Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

### Mechanical Specifications

<b>Maximum Loading</b>	Triple stack, 1-5/8 in cable
------------------------	------------------------------

### Packaging and Weights

<b>Height, packed</b>	4 cm   1.575 in
<b>Width, packed</b>	5 cm   1.969 in
<b>Length, packed</b>	1 cm   0.394 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.13 kg   0.287 lb

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value

# UAAI

---

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

