

FD3-AB096J00JKBP1



Enhanced Mini FDH 3000 Fiber Distribution Hub, 96-fiber shell, 96 fibers loaded, SC/APC, 100 ft distribution cable, dielectric loose tube, 12-fiber input cable

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Dielectric - Ribbon
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	96
Fibers per Distribution Cable, quantity	96
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole Wall
Splitter Slots, quantity	8

Dimensions

Height	584.2 mm 23 in
Width	330.2 mm 13 in
Depth	203.2 mm 8 in
Cable Length	30.48 m 100 ft
Enclosure Size	Mini

Material Specifications

Finish	Powder coated
Material Type	Aluminum

FD3-AB096J00JKBP1

Environmental Specifications

Environmental Space	Aerial
Qualification Standards	Telcordia GR-3123-CORE Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity	1
Packaging Type	Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

