

R8-CLAMP-4B



KwikClamp™ Hanger for RG8 cable, quadruple stack; includes hardware

Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm flat plate Round Member 8-25 mm

Dimensions

Maximum Stack Height	4
Height	192 mm 7.559 in
Width	32 mm 1.26 in
Length	42 mm 1.654 in
Compatible Diameter, maximum	12 mm 0.472 in
Compatible Diameter, minimum	9 mm 0.354 in
Nominal Size	3/8 in
Hanger Spacing, maximum	1.83 m 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

R8-CLAMP-4B

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 45

Weight, gross 8.97 kg | 19.775 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power