

FD5M-144S00DBB4P



Small FDH cabinet with 144 ports, LC/APC, no splitters, dry dielectric flat ribbon, 100 ft stub, 72F feeder, 144F distribution pole, wall mount

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution hub
Product Series	FDH 5000

General Specifications

Access	Front
Cable Type	Pigtails - Ribbon
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	144
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	72
Mounting	Wall/Pole Mount, mounting kit included
Splitter Slots, quantity	9

Dimensions

Height	609.6 mm 24 in
Width	336.55 mm 13.25 in
Depth	190.5 mm 7.5 in
Cable Length	30.48 m 100 ft
Enclosure Size	Small

Material Specifications

Finish	Powder coated
Material Type	Aluminum

FD5M-144S00DBB4P

Environmental Specifications

Environmental Space Above ground | Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

