

FD5M-576S00DDB5P



FDH5000 cabinet with 576 ports, LC/APC, no splitters, dry dielectric flat ribbon, 100 ft stub, 144F feeder, 288F distribution, pole mount

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution hub
Product Series	FDH 5000

General Specifications

Access	Front
Cable Type	Pigtails - Ribbon
Color	Putty white
Distribution Cables, quantity	2
Distribution Ports, quantity	576
Fibers per Distribution Cable, quantity	288
Fibers per Feeder Cable, quantity	144
Mounting	Pole
Splitter Slots, quantity	9

Dimensions

Height	698.5 mm 27.5 in
Width	698.5 mm 27.5 in
Depth	228.6 mm 9 in
Cable Length	30.48 m 100 ft
Enclosure Size	Large

Material Specifications

Finish	Powder coated
Material Type	Steel

FD5M-576S00DDB5P

Environmental Specifications

Environmental Space Above ground | Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

