M4800-PANELS



SYSTIMAX M4800 Series Modular Panels, 48 ports, for Cat 5E, 6, and 6A Jacks

Product Classification

PortfolioCommScope®Product TypeRJ45 patch panel

General Specifications

Rack Type EIA 19 in

Rack Units 1

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Steel

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

