

XP-2020-2025



Crossover Plate, joins 2-3/8 in or 2-7/8 in to 2-3/8 in or 2-7/8 in OD round members

Crossover kit that will accommodate 2-3/8 and 2-7/8" pipes in three combinations. It combines the functionality of the "XP-2020" and "XP-2025" in to one kit

- 2 3/8" mounted to 2 3/8" pipe
- 2 3/8" mounted to 2 7/8" pipe
- 2 7/8" mounted to 2 7/8" pipe

Product Classification

Product Type Clamp plate

General Specifications

Mounting Crossover plate

Dimensions

Mounting Diameter, maximum 73.025 mm | 2.875 in

Mounting Diameter, minimum 60.325 mm | 2.375 in

Material Thickness 9.525 mm | 0.375 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Plates | U-bolts

Packaging quantity 1