


# FGS-MHRT-M/F

---



FiberGuide® Horizontal T, 4x18in, 4x12in Exit, Yellow

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Tee
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Product Feature</b>	Transition
<b>Color</b>	Yellow
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Tee section

## Dimensions

<b>Height</b>	114 mm   4.488 in
<b>Width</b>	476 mm   18.74 in
<b>Length</b>	601 mm   23.661 in
<b>System Dimensions</b>	102 mm x 305 mm (4 in x 12 in)   102 mm x 457 mm (4 in x 18 in)

## Ordering Tree

# FGS-MHRT-M/F

9 10  
 FGS B - MHRT - H

## Section Color

9	empty	yellow
	B	black

## Section Size

10	A	4 x 4 in
	B	4 x 6 in
	B-VS	4 x 6 in, variable support bracket
	F	4 x 12 in
	F/B	4 x 12 in, 6 in exit
	F/B-S	4 x 12 in, 6 in exit, with variable support bracket
	F/B-VS	4 x 12 in, 6 in exit, variable support bracket
	F-VS	4 x 12 in, variable support bracket
	G	2 x 6 in
	H	4 x 24 in
	H/F	4 x 24 in, 12 in exit
	H/F-VS	4 x 24 in, 12 in exit, variable support bracket
	M	4 x 18 in
	M/F	4 x 18 in, 12 in exit
	M/H	4 x 18 in, 24 in exit
H/M	4 x 18 in	

\* Support brackets only come in black

## Material Specifications

**Material Type** Steel

## Environmental Specifications

**Safety Standard** CSA | UL

## Packaging and Weights

**Weight, net** 2.85 kg | 6.283 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

### Classification

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](https://www.commscope.com/ProductCompliance)

Compliant

Compliant

