FT-MP

Base Product



Field Term Modular Plug, RJ45

Product Classification	
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Modular plug
General Specifications	
ANSI/TIA Category	6 6A
Cable Type	Shielded Unshielded
Color	Clear
Conductor Type	Solid Stranded
Interface	RJ45
Positions/Loaded Contacts	8
Termination Type	IDC
Dimensions	
Contact Plating Thickness	1.27 μm
Compatible Conductor Gauge, solid	23 AWG 24 AWG
Material Specifications	
Contact Base Material	Copper alloy
Contact Plating Material	Gold over nickel
Material Type	Polycarbonate
Mechanical Specifications	

Plug Insertion Life, minimum

750 times

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 5, 2024



Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 93%, non-condensing
Safety Standard	UL 114344

Packaging and Weights

Packaging Type

Bag

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 5, 2024

