HFDC-48FIBER



HELIAX® Fiber Distribution Closure 48 fibers - 24 DLCs UPC.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Outdoor junction box

Product Brand HELIAX®

General Specifications

Application Used as a fiber junction box

Total Fiber Adapters 24
Color Black

Door, quantity 2

Mounting Pipe, 44–114 mm (1.75–4.5 in) OD | Wall

Total Fibers, quantity 48

Dimensions

 Height
 370.84 mm | 14.6 in

 Width
 215.9 mm | 8.5 in

 Depth
 113.03 mm | 4.45 in

 Jumper Breakout Length, Maximum
 85 mm | 3.346 in

Jumper Outlet, Quantity, Maximum 24

Jumper Outlet Diameter, Minimum 0 mm | 0 in

Jumper Outlet Diameter, Maximum5.5 mm | 0.217 inTrunk Entry, Diameter, Minimum5.5 mm | 0.217 inTrunk Entry, Diameter, Maximum17.5 mm | 0.689 in

Trunk Entry, Quantity, Maximum 4

Material Specifications

Material Type High-impact polycarbonate, UV resistant

Page 1 of 4

HFDC-48FIBER

Mechanical Specifications

Impact Test Method EN62262 | IEC62262: IK07

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Environmental Space Outdoor

Qualification Standards IEC 60529, IP68

Packaging and Weights

Included Mounting kit

Weight, net 3.946 kg | 8.7 lb

Included Products

FBR-COIL-S - HELIAX® Excess Discrete Fiber Coiling Reel, accommodates 16ft (5m) of excess 7mm fiber,

weights 5lbs fully populated, stackable, PIM free



FBR-COIL-S



HELIAX® Excess Discrete Fiber Coiling Reel, accommodates 16ft (5m) of excess 7mm fiber, weights 5lbs fully populated, stackable, PIM free

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Outdoor storage coil

Product Brand HELIAX®

General Specifications

Color Black

Mounting Angle iron | Pipe, 44–88.9 mm (1.75–3.5 in) OD

Dimensions

 Height
 203.2 mm | 8 in

 Width
 139.7 mm | 5.5 in

 Depth
 50.8 mm | 2 in

Material Specifications

Material Type Plastic

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Environmental Space Indoor | Outdoor

Packaging and Weights

IncludedMounting hardwareWeight, net0.454 kg | 1 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

Page 3 of 4

FBR-COIL-S

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant



