


MCHD-PK12S4-12-96



Four-sector HD Platform for 10" to 30" Monopoles, 12ft x 3.5" OD Face pipes, 2.88" OD Top Rail, includes (12) 2.88" OD x 96" antenna pipes

Product Classification

Product Type Monopole platform kit

General Specifications

Mounting Monopole, 254–762 mm (10–30 in) OD

Pipe, quantity 12

Sectors, quantity 4

Dimensions

Height 2,438.4 mm | 96 in

Face Width 3.81 m | 12.5 ft

Width 3810 mm | 150 in

Face Support Pipe Diameter 88.9 mm | 3.5 in

Mounting Diameter, maximum 762 mm | 30 in

Mounting Diameter, minimum 254 mm | 10 in

Pipe Outer Diameter 73.025 mm | 2.875 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Plain end pipes (12) | Platform | Rail | Ring mount

MCHD-PK12S4-12-96

Packaging quantity 1
Weight, net 1,542.668 kg | 3401 lb