

# SSH-2630

---



PIM-Guard®, SnapTak® Adjustable Hanger, Gen 2. Fits 26.0 mm to 30.0 mm Cables – PIM Free Polymer Construction. No Grommets Required.

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	PIM-Guard®   SnapTak®
<b>Ordering Note</b>	ANDREW® standard product (Global)

## General Specifications

<b>Accessories</b>	Hangers
<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Hanger Type</b>	Snap-in hanger
<b>Mounting</b>	3/4 in drilled cable ladder

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Maximum Stack Height, Coaxial</b>	3
<b>Height</b>	67.23 mm   2.647 in
<b>Width</b>	42 mm   1.654 in
<b>Length</b>	77.29 mm   3.043 in
<b>Compatible Cable Diameter Range</b>	26–30 mm
<b>Compatible Diameter, maximum</b>	30 mm   1.181 in
<b>Compatible Diameter, minimum</b>	26 mm   1.024 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

# SSH-2630

---

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥1000 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 4.5 cm | 1.772 in

**Width, packed** 20 cm | 7.874 in

**Length, packed** 30 cm | 11.811 in

**Packaging quantity** 10

**Weight, gross** 0.36 kg | 0.794 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power