CSC5-A5A1A1BAOOO



NOVUX™ CSC150 Compact Fiber Closure, slim trays with island, splice only, no adapters, no splitters, mounting bracket, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

Product Classification

Regional Availability

Asia | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Single-ended, rectangular fiber closure

Product Brand NOVUX™
Product Series CSC 150

General Specifications

 Cable Sealing Type
 Compressed gel

 Closure Sealing Type
 Hinged with latch

Closure Style Single-ended

Color Black

Mounting Pole | Wall

Port Type No adapter

Splicing Capacity, maximum 72
Splicing Capacity, Single Fusion, maximum 72

Splitter Type No splitter

Splitter, quantity 0

Dimensions

Height 357 mm | 14.055 in

COMMSCOPE®

CSC5-A5A1A1BA000

 Width
 185.4 mm | 7.299 in

 Depth
 115 mm | 4.528 in

Environmental Specifications

Environmental Space Outdoor

UV Resistance UV stabilized

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Packaging Type Box | Carton

