

760258637 | HCA-ACC-3mm Test Lead 6M ES00



3mm Test lead. Prodigy + SC/APC termination. with Full size and Bayonet converter included

- Prodigy converters simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability	EMEA
Product Type	Fiber test patch cord
Product Brand	PRODIGY™
Product Series	HCA

General Specifications

Color, boot A	Black
Color, connector A	Black
Color, connector B	Green
Interface, Connector A	Prodigy
Interface, Connector B	SC/APC
Jacket Color	Yellow

Mechanical Specifications

Dust Cap Pulling Force, minimum	300 N 67.443 lbf
--	--------------------

Optical Specifications

Insertion Loss, maximum	0.3 dB
Insertion Loss, typical	0.15 dB
Return Loss, minimum	65 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Indoor/Outdoor
Qualification Standards	IEC 60793 IEC 60794

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

