

A-100880

Base Product



Meter Cabinet with Backboard Only

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type Power supply enclosure

General Specifications

Access	Front door
Accessories	Cable plate In-ground root Plinth
Batteries Supported	0
Batteries Supported, with optional battery pedestal	0
Cabinet Type	Meter cabinet
Color	Green Green (RAL 6009) Light Gray (RAL 7035) Others available at additional cost
Door Security	7 mm triangle lock
Internal Mounting Surface	12 mm plywood backboard

Dimensions

Height	1016 mm 40 in
Width	660.4 mm 26 in
Depth	254 mm 10 in
Depth, without door	254 mm 10 in

Electrical Specifications

ac Feeds, Outgoing, quantity	0
Generator Connection	No connection

Material Specifications

Finish	Powder coated
Material Type	Galvanized steel

A-100880

Packaging and Weights

Weight, net

35.834 kg | 79 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system