

# RDT-SJ12J00C20020

---

RapidFiber® FDT Distribution Terminal, 12-fiber, SC/APC, 200 ft



## Product Classification

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Regional Availability</b> | EMEA   Latin America   North America |
| <b>Product Type</b>          | Fiber distribution terminal          |
| <b>Product Brand</b>         | RapidFiber®                          |
| <b>Product Series</b>        | FDT                                  |

## General Specifications

|                             |                                    |
|-----------------------------|------------------------------------|
| <b>Adapters, quantity</b>   | 12                                 |
| <b>Cable Color</b>          | Yellow                             |
| <b>Cable Entry Location</b> | Bottom left   Top left   Top right |
| <b>Cable Type</b>           | Indoor/outdoor - Stranded          |
| <b>Color</b>                | Putty white                        |
| <b>Front Cover Type</b>     | Hinged with lock                   |
| <b>Growth Configuration</b> | Fully loaded                       |
| <b>Interface</b>            | SC/APC                             |
| <b>Interface, stub</b>      | No connector                       |
| <b>Mounting</b>             | Wall                               |
| <b>Port, quantity</b>       | 12                                 |

## Dimensions

|                     |                  |
|---------------------|------------------|
| <b>Height</b>       | 152.4 mm   6 in  |
| <b>Width</b>        | 228.6 mm   9 in  |
| <b>Depth</b>        | 101.6 mm   4 in  |
| <b>Cable Length</b> | 60.96 m   200 ft |

# RDT-SJ12J00C20020

---

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

## Environmental Specifications

|                                |               |
|--------------------------------|---------------|
| <b>Environmental Space</b>     | Indoor        |
| <b>Qualification Standards</b> | NEMA, Type 12 |

## Packaging and Weights

|                           |          |
|---------------------------|----------|
| <b>Included</b>           | Grommets |
| <b>Packaging quantity</b> | 1        |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant  |

