

760231498 | SD-4U-FX



Standard Density 4U fixed Panel, accepts (12) LGX/1000 style footprint modules or panels, providing up to 144 duplex LC ports

OBSOLETE

This product was discontinued on: October 31, 2022

Replaced By:

760251051	EPX 4U fixed panel, accepts (12) LGX/PNL style splice cassettes, modules or panels, providing up to 144 duplex LC ports
EPX-4U-PNL-ENC-FX	

Product Classification

Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	SD

General Specifications

Application	Accepts twelve LGX/1000 footprint panels/cassettes
Color	Black
Interface, front	Unloaded
Rack Units	4
Shelf Movement	Fixed

Dimensions

Height	177.8 mm 7 in
Width	482.6 mm 19 in
Depth	485.14 mm 19.1 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC) Steel
----------------------	--

Environmental Specifications

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1

Weight, net 9.299 kg | 20.5 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

