

760241534 | FD-8-1U-B



1RU patch panel which interfaces with MPO-8 ports including QSFP to easily break them out into LC connections. The MPO and shuttered LC ports are both front facing for easy mapping and patching. 10 singlemode MPO-8 and 40 duplex LC ports, Enhanced Method

1RU patch panel which interfaces with MPO-8 ports including QSFP to easily break them out into LC connections. The MPO and shuttered LC ports are both front facing for easy mapping and patching. 10 singlemode MPO-8 and 40 duplex LC ports, Enhanced Method B

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FD

General Specifications

Color	Black
Interface, front	LC/UPC MPO
Interface Feature, front	Pinned
Rack Units	1
Shelf Movement	Fixed
Total Ports, quantity	40

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	292.1 mm 11.5 in

Optical Specifications

Insertion Loss, maximum	0.6 dB
--------------------------------	--------

Environmental Specifications

Safety Standard	UL 60950
------------------------	----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

