


FCM-100000-IP12



FCM InstaPATCH (IP), 12 IP modules, empty panel, 23" rack mtg, 8" height

- Compatible with 3mm MPO Patchcord, trunk cables, 1.6-2mm SC/LC patchcord, 900µm SC/LC stranded cable
- Mounts to rear mounting flange
- Compatible with any 360 (DM & DP) distribution module and distribution panel
- Panel designed specifically for rear load style fiber frames (e.g. E-501-L91)

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FDF

General Specifications

Functionality	Patching
Application	Accepts twelve 360 modules or MPO panels Used in rear-load FDF-style frames only
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Growth Configuration	Unloaded
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 23 in
Rack Units	4.57
Shelf Movement	Fixed
Total Ports, quantity	12

Dimensions

Height	203.2 mm 8 in
Width	584.2 mm 23 in
Depth	304.8 mm 12 in

Material Specifications

FCM-100000-IP12

Finish	Powder coated
Material Type	Steel

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

