

FPS-FMTSP-EJJ01



FMT Fiber Optic Splitter Patch Panel, 1U, 19 in, 2 x 32 splitter, SC/APC splitter and output connect., 1 splitter

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Splitter patch panel
Product Series	FMT

General Specifications

Device Type	Patch panel
Functionality	Splitting
Access	Front
Circuits, quantity	1
Distribution Type	2 x 32 splitter
Interface, front	SC/APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	71.88 mm 2.83 in
Width	17.27 mm 0.68 in
Depth	177.8 mm 7 in

Optical Specifications

Directivity, minimum	60 dB
Polarization Dependent Loss, maximum	0.4 dB
Uniformity, maximum	2 dB
Wavelength Range	1260–1635 nm
Insertion Loss, Splitter, maximum	17.4 dB
Insertion Loss, Splitter, typical	16.2 dB

FPS-FMTSP-EJJ01

Return Loss, Splitter, minimum 55 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

