


NG4-APLC120000



NG4access® Adapter Pack Universal Kit, 2 blocks with 12 LC Adapter positions each

- Adapter ports are staggered for easy connector insertion/removal, and help to clearly identify individual adapter ports
- Each chassis can be loaded with up to 48 adapter packs while two adapter packs snap into a single access tray

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber adapter pack
Product Brand	NG4access®
Product Series	FACT NG4

General Specifications

Application	For use with NG4 panels
Adapters, quantity, front	6
Body Style	Duplex Straight orientation
Color, front	Putty white
Interface	LC/UPC
Total Ports, quantity, front	12

Optical Specifications

Fiber Mode	Multimode Singlemode
-------------------	------------------------

Environmental Specifications

Operating Temperature	-5 °C to +40 °C (+23 °F to +104 °F)
Storage Temperature	-5 °C to +50 °C (+23 °F to +122 °F)

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

NG4-APLC120000

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

